

760255092 | PPL-SP-24LC-SM-PT-BEU-ANT



Propel Singlemode Splice Cassette, 24LC/UPC with internal shutters, 250 μm OS2 single fiber pigtailed, Method B Enhanced ULL, ANT Splice Protector

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250 μm or 900 μm incoming fiber

Recommended for use with 24f subunit cable

Product Classification

Regional Availability	Europe
Portfolio	CommScope®
Product Type	Fiber cassette with pigtailed
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	67.31 mm 2.65 in
Width	196.012 mm 7.717 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL

Packaging and Weights

Included ANT holder | ANT mechanical splice protection

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

