

# 760255094 | PPL-SP-24LC-OM5-PT-BEU-ANT



Propel Multimode Splice Cassette, 24LC with internal shutters, OM5 single fiber pigtailed, Method B Enhanced ULL, ANT Splice Protector

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250  $\mu\text{m}$  or 900  $\mu\text{m}$  incoming fiber

Recommended for use with 24f subunit cable

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Regional Availability</b> | Europe                        |
| <b>Portfolio</b>             | CommScope®                    |
| <b>Product Type</b>          | Fiber cassette with pigtailed |
| <b>Product Brand</b>         | Propel                        |
| <b>Product Series</b>        | PPL                           |

## General Specifications

|                               |                         |
|-------------------------------|-------------------------|
| <b>Color, front</b>           | Lime green              |
| <b>Interface, front</b>       | LC/UPC                  |
| <b>Interface, rear</b>        | Stranded pigtail        |
| <b>Polarity</b>               | Method B Enhanced (ULL) |
| <b>Shuttered</b>              | Yes                     |
| <b>Total Fibers, quantity</b> | 24                      |

## Dimensions

|               |                       |
|---------------|-----------------------|
| <b>Height</b> | 67.31 mm   2.65 in    |
| <b>Width</b>  | 196.012 mm   7.717 in |

## Optical Specifications

|                                |           |
|--------------------------------|-----------|
| <b>Fiber Mode</b>              | Multimode |
| <b>Fiber Type</b>              | G.657.A2  |
| <b>Insertion Loss, maximum</b> | 0.15 dB   |

## Environmental Specifications

# 760255094 | PPL-SP-24LC-OM5-PT-BEU-ANT

---

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** UL

## Packaging and Weights

**Included** ANT holder | ANT mechanical splice protection

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

