

# 760256512 | RP-MOD-012-TS-MPO-LC02-BEU-YL



ReadyPATCH® ULL Singlemode MPO-12 Distribution Module, 6 duplex LC non-keyed yellow adapters to 1X12f MPO/UPC non-pinned, Method B Enhanced

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	ReadyPATCH®

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	1
<b>Color, front</b>	Yellow
<b>Color, rear</b>	Black
<b>Data Module Type</b>	Standard
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	MPO Non-Pinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	12
<b>Total Ports, quantity, front</b>	6

## Dimensions

<b>Height</b>	27.94 mm   1.1 in
<b>Width</b>	129.54 mm   5.1 in
<b>Depth</b>	127 mm   5 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum</b>	0.6 dB

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

