

FD3-MN432J00M0MFOC



Indoor FDH 3000 w/ 432f Shell, 432f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Spliced Ribbon Pigtails

Indoor FDH 3000 w/ 432f Shell, 432f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Spliced Ribbon Pigtails

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Functionality	Patching Splicing
Adapters, quantity	432
Color	Putty white
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	432

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

FD3-MN432J00M0MFOC

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Above maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

Compliant/Exempted

