

F1-CLAMP-1B

KwikClamp™ Hanger for 1/4 in superflexible coaxial cable, single stack; includes hardware



Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8–25 mm

Dimensions

Maximum Stack Height	1
Height	99 mm 3.898 in
Width	22 mm 0.866 in
Length	42 mm 1.654 in
Compatible Diameter, maximum	9 mm 0.354 in
Compatible Diameter, minimum	7 mm 0.276 in
Nominal Size	1/4 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

F1-CLAMP-1B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 120

Weight, gross 7.5 kg | 16.535 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power