


R8-CLAMP-2B



KwikClamp™ Hanger for RG8 cable, double stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	2
Height	138 mm 5.433 in
Width	32 mm 1.26 in
Length	42 mm 1.654 in
Compatible Diameter, maximum	11 mm 0.433 in
Compatible Diameter, minimum	10 mm 0.394 in
Nominal Size	3/8 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel
----------------------	--------------------------------------

R8-CLAMP-2B

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 60

Weight, gross 7.7 kg | 16.976 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power