

F-CLAMP-C-2B



KwikClamp™ Hanger for power & fiber cables, 22–34 mm, double stack; includes hardware

Product Classification

| | |
|----------------------|--|
| Product Type | Hanger kit |
| Product Brand | KwikClamp™ |
| Ordering Note | CommScope® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box |

General Specifications

| | |
|--------------------------|--|
| Cables per Hanger | 1 |
| Color | Black |
| Hanger Type | KwikClamp™ hanger |
| Mounting | 3–25 mm angle iron 3–25 mm flat plate Round Member 8-25 mm |

Dimensions

| | |
|--|-------------------|
| Maximum Stack Height | 2 |
| Height | 192 mm 7.559 in |
| Width | 45 mm 1.772 in |
| Length | 44 mm 1.732 in |
| Compatible Cable Diameter Range | 22–34 mm |
| Compatible Diameter, maximum | 34 mm 1.339 in |
| Compatible Diameter, minimum | 22 mm 0.866 in |
| Hanger Spacing, maximum | 1.83 m 6.004 ft |

Electrical Specifications

| | |
|------------------------------------|--------|
| Return Loss Effect, maximum | 0.1 dB |
| DTF Effect, maximum | 0.1 dB |

F-CLAMP-C-2B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 27

Weight, gross 5.6 kg | 12.346 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power