

HG-MSF-158



Grommet with 1 x 25 mm, 1 x 14 mm, 1 x 12 mm, 1 x 10 mm, 1 x 8 mm and 1 X 6 mm holes for 1-5/8 in SnapStack or Click-on Hanger

Product Classification

Product Type	Grommet
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Adapter Type	Adapter
Cables per Hanger	6
Color	Black

Dimensions

Height	55.626 mm 2.19 in
Width	54.864 mm 2.16 in
Compatible Diameter, maximum	24.994 mm 0.984 in
Compatible Diameter, minimum	5.842 mm 0.23 in
Diameter Range (cable 1)	6 mm
Diameter Range (cable 2)	14 mm
Nominal Size	1-5/8 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Packaging and Weights

Packaging quantity	10
Weight, gross	0.86 kg 1.896 lb

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

HG-MSF-158

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant