

VSRAL-TS-B



Adjustable V-Stabilizer™ for a Tower, large leg size (8–16 in)

Product Classification

Portfolio	CommScope®
Product Type	Reinforcement kit
Ordering Note	CommScope® standard product (Global)
Warranty	One year

General Specifications

Mounting	Angle 60°, 406.4 mm (16 in) Angle 90°, 304.8 mm (12 in) Straight or tapered legs up to 406.4 mm (16 in) OD
Pipe, quantity	0
Tower Taper	Non-tapered Tapered

Dimensions

Face Width	4.42 m 14.5 ft
Length	2032 mm 80 in
Mounting Diameter, maximum	406.4 mm 16 in
Mounting Diameter, minimum	203.2 mm 8 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Packaging and Weights

Included	Clamps Legs
Packaging quantity	1
Weight, net	35.38 kg 78 lb

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

VSRAL-TS-B

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Warranty For more information, please consult our Product Warranty guidelines