



Outdoor Fiber Cable, 96-fiber, singlemode OS2, loose tube, blue

Product Classification

Regional Availability	Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LD

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Blue
Jacket Marking	Meters
Fibers per Subunit, quantity	6
Total Fiber Count	96

Dimensions

Diameter Over Jacket	8.9 mm 0.35 in
-----------------------------	------------------

Material Specifications

Jacket Material	Nylon
------------------------	-------

Mechanical Specifications

Flex	25 cycles
-------------	-----------

Optical Specifications

Fiber Type	G.652.D OS2
-------------------	---------------

Optical Specifications, Wavelength Specific

Standards Compliance	TIA-492CAAB (OS2)
-----------------------------	-------------------

Environmental Specifications

Operating Temperature -10 °C to +70 °C (+14 °F to +158 °F)

Environmental Space Buried

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable