


FD3-AC144J00DBBP2P-US



Standard FDH3000, 144F loaded pole mounted cabinet, SC/APC, PNP splitter capable, OSP Dry Dielectric Flat Ribbon Cable, 100 ft stubs, using a 1x144F distribution cable assembly and a 1x24F feeder, Build America Buy America (BABA) Compliant

- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

| | |
|--------------------------------|---|
| Regional Availability | North America |
| Product Type | Fiber distribution hub |
| Product Series | FDH 3000 |
| Government Requirements | Build America Buy America (BABA) coming soon* |

General Specifications

| | |
|--|-------------------------|
| Access | Front |
| Cable Type | Dry Dielectric - Ribbon |
| Color | Putty white |
| Distribution Cables, quantity | 1 |
| Distribution Ports, quantity | 144 |
| Fibers per Distribution Cable, quantity | 144 |
| Fibers per Feeder Cable, quantity | 24 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Location of Manufacturing | Coming soon |
| Mounting | Pole |
| Splitter Slots, quantity | 18 |

Dimensions

| | |
|---------------|------------------|
| Height | 914.4 mm 36 in |
| Width | 533.4 mm 21 in |

FD3-AC144J00DBBP2P-US

| | |
|-----------------------|------------------|
| Depth | 355.6 mm 14 in |
| Cable Length | 30.48 m 100 ft |
| Enclosure Size | Extra small |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Aluminum |

Environmental Specifications

| | |
|----------------------------|-----------------------|
| Environmental Space | Above ground Aerial |
|----------------------------|-----------------------|

Packaging and Weights

| | |
|---------------------------|--------|
| Packaging quantity | 1 |
| Packaging Type | Pallet |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

