

# FD3-AG432J00TBBP4-US



Standard FDH3000, 432F loaded pad/vault mounted cabinet, SC/APC, PNP splitter capable, OSP Dry Dielectric Flat Ribbon Cable, 100 ft stubs, using a 3x144F distribution cable assembly and a 1x48F feeder, Build America Buy America (BABA) Compliant

- \*CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000
<b>Government Requirements</b>	Build America Buy America (BABA) coming soon*

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Dry Dielectric - Ribbon
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	3
<b>Distribution Ports, quantity</b>	432
<b>Fibers per Distribution Cable, quantity</b>	144
<b>Fibers per Feeder Cable, quantity</b>	48
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Location of Manufacturing</b>	Coming soon
<b>Mounting</b>	Pad
<b>Splitter Slots, quantity</b>	30

## Dimensions

<b>Height</b>	1,066.8 mm   42 in
<b>Width</b>	685.8 mm   27 in

# FD3-AG432J00TBBP4-US

---

<b>Depth</b>	457.2 mm   18 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Medium

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Environmental Specifications

<b>Environmental Space</b>	Above ground
----------------------------	--------------

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

