

RT-NF11-3-120



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 11 ft face, three 2-7/8 in OD x 120 in pipes

Product Classification

Product Type	Non-penetrating roof frame
Product Brand	PIM-guard

General Specifications

Mounting	Non-penetrating
Pipe, quantity	3

Dimensions

Height	3,048 mm 120 in
Face Width	3.353 m 11 ft
Width	3,352.8 mm 132 in
Length	2.377 m 7.8 ft
Pipe Length	3,048 mm 120 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

RT-NF11-3-120

Included	Ballast tray Frame Plain end pipes (3)
Packaging quantity	1
Weight, net	484.6 kg 1,068.359 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--