


# RT-NF13-B

---



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 13 ft face, Base Frame Only

## Product Classification

<b>Product Type</b>	Non-penetrating roof frame
<b>Product Brand</b>	PIM-guard

## General Specifications

<b>Mounting</b>	Non-penetrating
<b>Pipe, quantity</b>	0

## Dimensions

<b>Height</b>	2,252.98 mm   88.7 in
<b>Face Width</b>	3.962 m   13 ft
<b>Width</b>	3,962.4 mm   156 in
<b>Length</b>	2.377 m   7.8 ft
<b>Pipe Length</b>	0 mm   0 in
<b>Face Support Pipe Diameter</b>	73.152 mm   2.88 in
<b>Pipe Outer Diameter</b>	73.152 mm   2.88 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact <a href="mailto:steelproducts@commscope.com">steelproducts@commscope.com</a> or call 800-255-1479
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

# RT-NF13-B

---

<b>Included</b>	Ballast tray   Frame
<b>Packaging quantity</b>	1
<b>Weight, net</b>	387.77 kg   854.885 lb

\* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--