


UGBKIT-0420-G

Galvanized Ground Buss Bar Kit, 1/4 in x 4 in x 20 in



Product Classification

Product Type	Grounding bar
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

Dimensions

Height	101.6 mm 4 in
Length	508 mm 20 in
Material Thickness	6.35 mm 0.25 in
Hole Size	7/16 in 7/16 in x 5/8 in
Hole Distance, center to center	19.05 mm 0.75 in

Material Specifications

Material Type	Galvanized steel
----------------------	------------------

Packaging and Weights

Included	Galvanized angle adapter Grounding bar Insulators Mounting brackets Universal hardware
Packaging quantity	1

Included Products

GB-HK-DPU	– Universal Buss Bar Installation Hardware Kit, UL467 Compliant
-----------	---

GB-HK-DPU



Universal Buss Bar Installation Hardware Kit, UL467 Compliant

Product Classification

Product Type	Attachment kit
Product Brand	HELIAX®
Ordering Note	CommScope® standard product in the United States and Canada

General Specifications

Accessories	Grounding Bars
--------------------	----------------

Packaging and Weights

Height, packed	170.18 mm 6.7 in
Width, packed	129.54 mm 5.1 in
Length, packed	99.06 mm 3.9 in
Included	Angle adapters Drive pin anchor Insulators, Mounting brackets Universal hardware
Packaging quantity	1
Weight, gross	2.6 kg 5.732 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

