

# 860649813 | Round Straight 10.75" Diameter Pole 24' Lum mount

---



10.75" diameter pole that accomodates Small Cell equipment and Smart City devices

Metal pole that supports a variety of installation methods such as poured concrete, embedded pole, pre-cast, and helical foundations  
Configurable color and pole height  
22' and 25' Poles do not have luminaire mounts

Foundation Kit Ordered Separately

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Standard poles
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Color</b>	Galvanized
<b>Color Options</b>	Antique Bronze (SRSL 45893)   Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Fairfax Brown (SW 2856)   Faux Concrete   Federal Park Brown   Green (RAL 6005)   Light Gray (RAL 7035)   Metallic Silver   Signal Black (RAL 9004)   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Compatible Foundation Type</b>	Embedded Pole   Embedded with Foam   Helical Anchor   Poured Concrete   Pre-Cast Concrete   Split Helical Anchors
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI

## Dimensions

<b>Pole Height Options</b>	10.668 m   35 ft   11.278 m   37 ft   12.192 m   40 ft   6.706 m   22 ft   7.62 m   25 ft   8.23 m   27 ft   8.534 m   28 ft   9.144 m   30 ft   9.754 m   32 ft
<b>Width</b>	273.05 mm   10.75 in
<b>Luminaire Mount Height</b>	7.315 m   24 ft
<b>Mounting Bolt Circle Diameter</b>	406.4 mm   16 in

# 860649813 | Round Straight 10.75" Diameter Pole 24' Lum mount

---

# 860649813 | Round Straight 10.75" Diameter Pole 24' Lum mount

## Ordering Tree



Pole Color	
1	Light Grey (RAL 7035)
2	Green (RAL 6005)
3	Black (RAL 9005)
4	Brown (RAL 8014)
5	Beige Grey (RAL 7006)
6	Fairfax Brown (SW 2856)
8	Federal Park Brown
9	Metallic Silver
20	Umbra Grey (RAL 7022)
C	Faux Concrete
F	Signal Black (RAL 9004)
G	Black Green (RAL 6012)
W	White (RAL 9010)
Z	Antique Bronze (SRSL 45893)
0	Galvanized

Pole Height	
22	22 feet (6.7 meters)
25	25 feet (7.6 meters)
27	27 feet (8.2 meters)
28	28 feet (8.5 meters)
30	30 feet (9.1 meters)
32	32 feet (9.8 meters)
35	35 feet (10.7 meters)
37	37 feet (11.3 meters)
40	40 feet (12.2 meters)

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Included Products

860644785-CK BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES	-	BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES
--	---	--

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
<b>Pole Height Options</b>	Overall AGL Standard Height