

# 860650199 | Square 6"X6"



6" X 6" Square pole that accomodates Small Cell equipment and Smart City devices

Metal pole that supports a variety of installation methods such as poured concrete, embedded pole, pre-cast, and helical foundations  
Break Away Compatible  
Accommodates Pole Top Concealment and antenna mounts  
Configurable color and pole height

Foundation Kit Ordered Separately

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Standard poles
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Galvanized
<b>Color Options</b>	Antique Bronze (SRSL 45893)   Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Fairfax Brown (SW 2856)   Faux Concrete   Federal Park Brown   Green (RAL 6005)   Light Gray (RAL 7035)   Metallic Silver   Signal Black (RAL 9004)   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Compatible Foundation Type</b>	Embedded Pole   Embedded with Foam   Helical Anchor   Poured Concrete   Pre-Cast Concrete   Split Helical Anchors
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI


## Dimensions

<b>Pole Height Options</b>	6.096 m   20 ft   7.62 m   25 ft   9.144 m   30 ft
<b>Width</b>	152.4 mm   6 in

# 860650199 | Square 6"X6"

<b>Depth</b>	152.4 mm   6 in
<b>Luminaire Mount Height</b>	5.791 m   19 ft   7.315 m   24 ft   8.839 m   29 ft
<b>Mounting Bolt Circle Diameter</b>	406.4 mm   16 in

## Ordering Tree



## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
<b>Pole Height Options</b>	Overall AGL Standard Height