

Antenna Enclosure Kit

- Innovative flexible modular solution enabling suitable sites to be upgraded to 5G capability
- A selection of 3.5GHz Passive or Active mMIMO antennas are compatible and easily installed in the AEKT module
- The module installs directly above an existing, suitable passive antenna to provide the appearance of a single integrated antenna unit potentially simplifying site zoning approvals
- Installed antenna units can be swapped out on site e.g. to perform capacity upgrades
- Compatible specifically with antennas featuring CommScope's 498 x 197 mm (WxD) radome housing
- Can be deployed as a standalone solution
- Includes Antenna Enclosure Housing, Installation Kit for CommScope 3.5GHz Antenna (Types S4-90M-R1-V2, S4-90M-R1-V3 or S4-90M-R1-V4), AEKT Mounting Hardware, protective "Windshield" Panels and Top Cap
- Installation Kit for suitable mMIMO Active Antennas to be ordered separately when required
- A Mounting Kit for the antenna installed below the AEKT unit should be ordered separately, Commscope P/N: BSAMNT-AEKT (required when installing the AEKT module directly on top of an antenna)
- Contact your CommScope representative for further details

General Specifications

Antenna Type	Antenna enclosure kit	
Color	Light Gray (RAL 7035)	
Performance Note	Outdoor usage	
Radome Material	Fiberglass, UV resistant	
Dimensions		
Width	498 mm 19.606 in	


Depth	199 mm 7.835 in
Length	1100 mm 43.307 in
Net Weight, without mounting kit	9.29 kg 20.481 lb

Application Drawing

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 19, 2024



AEKT



Mechanical Specifications

Wind Loading @ Velocity, frontal Wind Loading @ Velocity, lateral Wind Loading @ Velocity, rear 700.0 N @ 150 km/h (157.4 lbf @ 150 km/h) 308.0 N @ 150 km/h (69.2 lbf @ 150 km/h) 700.0 N @ 150 km/h (157.4 lbf @ 150 km/h)

Packaging and Weights

Width, packed	620 mm 24.409 in
Depth, packed	350 mm 13.78 in
Length, packed	1430 mm 56.299 in
Included	Brackets Hardware
Weight, gross	25.46 kg 56.13 lb

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 19, 2024



AEKT

Weight, net

19.17 kg | 42.263 lb

Regulatory Compliance/Certifications

Classification

CE

Agency

Compliant with the relevant CE product directives

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

AEKTMNT

CE

 Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 19, 2024



AEKTMNT



Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members

• Kit contains two mounting bracket sets for round members and two brackets to install antenna types S4-90M-R1-V2, S4-90M-R1-V3 or S4-90M-R1-V4 inside the AEKT module

Product Classification			
Product Type	Pipe mounting kit		
General Specifications			
Application	Outdoor		
Color	Silver		
Dimensions			
Compatible Diameter, maximum 114.3 mm 4.5 ii			
Compatible Diameter, minimum	61 mm 2.402 in		
Weight, net	9.3 kg 20.503 lb		
Material Specifications			
Material Type	Galvanized steel		

Packaging and Weights

Included	Brackets	I	Hardware
Packaging quantity	1		

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024

