

1754845-1



LightCrimp Plus™ Fiber Optic Connector Termination Tool Kit, LC/SC, without microscope

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber tool kit |
| Product Brand | LightCrimp Plus™ |
| Product Series | LightCrimp |

General Specifications

| | |
|------------------|---------|
| Interface | LC SC |
|------------------|---------|

Environmental Specifications

| | |
|----------------------------|--------|
| Environmental Space | Indoor |
|----------------------------|--------|

Packaging and Weights

| | |
|-----------------|---|
| Included | Alcohol fiber wipes Ball and hex key Carrying case Fiber cleaver Instruction sheet Kevlar cutter LC+ LC/SC cable holder Miller dual-hole strip tool Pro-crimper, LC+ LC/SC /Splice Slitter tool, 2 mm and 3 mm Stripper, micro-strip W/.008BLA Wrench, open end ¼ |
|-----------------|---|

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications


| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

1754845-1



Included Products

- 760243578 – Fiber Optic Hand Held Precision Cleaver Tool



Fiber Optic Hand Held Precision Cleaver Tool

- Provides operator-independent precision quality cleaves in a hand held size
- Includes a blade knife with a 48,000 cleave lifetime
- Suited for field installable mechanical splice connectors, bare fiber adapters and fusion and mechanical splicing
- Supplied with a padded belt case with neck lanyard for convenience and storage

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber tool kit |

Dimensions

| | |
|---------------|------------------|
| Height | 46 mm 1.811 in |
| Width | 53 mm 2.087 in |
| Length | 55 mm 2.165 in |

Environmental Specifications

| | |
|----------------------------|--------|
| Environmental Space | Indoor |
|----------------------------|--------|

Packaging and Weights

| | |
|---------------------------|------------------|
| Packaging quantity | 1 |
| Weight, net | 500 g 1.102 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

