

# EPX fiber panels

CommScope EPX fiber panels offer great application flexibility with the use of interchangeable adapter packs, splice cassettes and splitter modules.

## FEATURES AND BENEFITS:


- Compact, lightweight panel designed for operational simplicity
- Interchangeable adapter packs, splice cassettes and/or splitter modules
- Available with LGX adapter styles in 1U, 2U or 4U in either fixed or sliding configurations
- Legacy LGX compatibility

## Enclosed Panels




MID	Description	RU	Bulkhead	# of Adapter plates	H"	W"	D"
760249997	EPX-1U-PNL-ENC	1	Fixed	3	1.75	19	16.25
760251043	EPX-1U-PNL-ENC-FX	1	Sliding	3	1.75	19	16.25
760251045	EPX-2U-PNL-ENC	2	Fixed	6	1.75	19	16.25
760251047	EPX-2U-PNL-ENC-FX	2	Sliding	6	1.75	19	16.25
760251049	EPX-4U-PNL-ENC	4	Fixed	12	1.75	19	16.25
760251051	EPX-4U-PNL-ENC-FX	4	Sliding	12	1.75	19	16.25

## Wall Boxes



MID	Description	# of Adapter plates	H"	W"	D"
760248905	WB2-EMT-BK-2P-PNL	2	11.22	14.46	2.08
760248907	WB2-EMT-BK-8P-PNL	8	11.22	14.46	6.25

## Adapter Plates



MID	Description	Adapter style	Interface	# of Adapter plates	Patching style
<a href="#">760148213</a>	PNL-BK-006-SFA-SC06-BL	SC	UPC	6	Simplex
<a href="#">760242756</a>	PNL-BK-012-SFA-SC 12-BL	SC	UPC	12	Simplex
<a href="#">760147652</a>	PNL-BK-006-AFA-SC06-GR	SC	APC	6	Simplex
<a href="#">760242438</a>	PNL-BK-012-SFA-SC 12-GR	SC	APC	12	Simplex
<a href="#">760245075</a>	PNL-BK-006-SFA-LC02-BL-NS	LC	UPC	3	Duplex
<a href="#">760149351</a>	PNL-BK-012-SFA-LC02-BL-NS	LC	UPC	6	Duplex
<a href="#">760148361</a>	PNL-BK-024-SFA-LC02-BL-NS	LC	UPC	12	Duplex
<a href="#">760245076</a>	PNL-BK-006-KFA-LA02-GR-NS	LC	APC	3	Duplex
<a href="#">760147801</a>	PNL-BK-012-KFA-LA02-GR-NS	LC	APC	6	Duplex
<a href="#">760147900</a>	PNL-BK-024-KFA-LC02-GR-NS	LC	APC	12	Duplex

## Splicing cassette



MID	Description	Adapter style	Interface	# of Adapter plates	Pigtail
<a href="#">760221788</a>	PNL-CS-12SCW-PT	SC	UPC	12	Stranded 900um
<a href="#">760222604</a>	PNL-CS-12SAW-PT	SC	APC	12	
<a href="#">760221747</a>	PNL-CS-12LCW-PT	LC	UPC	12	
<a href="#">760221705</a>	PNL-CS-24LCW-PT	LC	UPC	24	
<a href="#">760222596</a>	PNL-CS-12LAW-PT	LC	APC	12	
<a href="#">760222588</a>	PNL-CS-24LAW-PT	LC	APC	24	

## Splitter Guide



[Click to download](#)



# COMMSCOPE®

commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2023 CommScope, Inc. All rights reserved.

CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners.

PA-1178891-EN (09/23)