

760027441 | PNL-BK-024-MFA-LC02-BG-SHUTTERED



Adapter Pack, 1000-type, with 12 OptiSPEED® Multimode duplex LC adapters, beige

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber adapter pack |
| Product Brand | OptiSPEED® |
| Product Series | 1000-style |

General Specifications

| | |
|------------------------------------|--|
| Application | Used in conjunction with G2 1U, 2U and 4U adapter panel shelves, surface mount and raised floor enclosures |
| Adapter Color | Beige |
| Adapter Cutout, quantity | 24 |
| Adapters, quantity | 12 |
| Body Style | Duplex |
| Interface | LC/UPC |
| Pigtails Included, quantity | 0 |
| Shuttered | Yes |

Optical Specifications

| | |
|-------------------|-----------|
| Fiber Mode | Multimode |
|-------------------|-----------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

760027441 | PNL-BK-024-MFA-LC02-BG-SHUTTERED



Included Products

760056010 – OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack
MFA-LC02-BG/LP-SHUTTERED

760056010 | MFA-LC02-BG/LP-SHUTTERED



OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber adapter |
| Product Brand | OptiSPEED® |
| Product Series | MFA |

General Specifications

| | |
|-------------------------------|---------------------------------------|
| Body Style | Duplex |
| Color | Beige |
| Interface | LC/UPC |
| Interface Feature | Reduced footprint |
| Mounting | No flange |
| Shuttered | Yes |
| Total Ports, quantity | 2 |
| Transmission Standards | TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3 |

Material Specifications

| | |
|----------------------------------|--------------------|
| Alignment Sleeve Material | Phosphorous bronze |
|----------------------------------|--------------------|

Optical Specifications

| | |
|-------------------|-----------|
| Fiber Mode | Multimode |
|-------------------|-----------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

