

760028357 | PNL-BK-024-AFA-LC02-GR-SHUTTERED



Adapter Pack, Black, 1000-Type, with 12 TeraSPEED® Singlemode duplex LC/APC Adapters, green, shuttered

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter pack
Product Brand	TeraSPEED®
Product Series	1000-style

General Specifications

Application	Used in conjunction with G2 1U, 2U and 4U adapter panel shelves, surface mount and raised floor enclosures Used in conjunction with panels and enclosures (rack, wall, and floor mount) that accept 1000 style panels
Adapter Color	Green
Adapter Cutout, quantity	24
Adapters, quantity	12
Body Style	Duplex
Interface	LC/APC
Pigtails Included, quantity	0
Shuttered	Yes
Total Ports, quantity	12

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

760028357 | PNL-BK-024-AFA-LC02-GR-SHUTTERED

ROHS Compliant


UK-ROHS Compliant



Included Products

760056036 – TeraSPEED® LC-APC Duplex Low Profile Suttered Adapter, Green, Single Pack
AFA-LC02-GR/LP-SHUTTERED

760056036 | AFA-LC02-GR/LP-SHUTTERED



TeraSPEED® LC-APC Duplex Low Profile Shuttered Adapter, Green, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	TeraSPEED®
Product Series	AFA

General Specifications

Body Style	Duplex
Color	Green
Interface	LC/APC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

760056036 | AFA-LC02-GR/LP-SHUTTERED

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

