# MT-219-72

Pipe Mount Kit, 2-3/8 in OD x 72 in

Product Classification

Product Type	Pipe mount kit

General Specifications

Mounting	Pipe, 88.9 mm (3-1/2 in) OD
Pipe, quantity	1

Dimensions

Height	1,828.8 mm | 72 in
Width	127 mm | 5 in
Length	127 mm | 5 in
Pipe Length	1,828.8 mm | 72 in
Pipe Outer Diameter	60.96 mm | 2.4 in

Material Specifications

Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Crossover bracket | Plain end pipes | U-bolts
Packaging quantity	1
Weight, net	14.9 kg | 32.849 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

MT-219-H	–	Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not

COMMSCOPE®

included

MT-651   –   Plain End Pipe, 2-3/8 in OD x 72 in .120" A500C 46Ksi

COMMSCOPE®

MT-219-H

Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not included

Product Classification

Product Type	Pipe mount kit

General Specifications

Mounting	Pipe, 60.3 mm (2-3/8 in) OD | Pipe, 88.9 mm (3-1/2 in) OD

Dimensions

Height	254 mm | 10 in
Width	127 mm | 5 in
Length	127 mm | 5 in
Mounting Diameter, maximum	88.9 mm | 3.5 in
Mounting Diameter, minimum	60.325 mm | 2.375 in

Material Specifications

Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Crossover bracket | U-bolts
Packaging quantity	1
Weight, net	4.9 kg | 10.803 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

COMMSCOPE®

MT-651

Plain End Pipe, 2-3/8 in OD x 72 in .120" A500C 46Ksi

Product Classification

Product Type	Plain end pipe

General Specifications

Pipe, quantity	1

Dimensions

Height	60.96 mm | 2.4 in
Width	60.96 mm | 2.4 in
Length	1,828.8 mm | 72 in
Pipe Length	1,828.8 mm | 72 in
Pipe Outer Diameter	60.96 mm | 2.4 in
Material Thickness	3.048 mm | 0.12 in

Material Specifications

Material Type	A500 | Hot dip galvanized steel
Material Grade	C
Material Strength	46 KSI

Packaging and Weights

Included	Pipe
Packaging quantity	1
Weight, net	8 kg | 17.637 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®

MT-651

| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

COMMSCOPE®