

4-port sector antenna, 4x 694-960 MHz, 65° HPBW

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Tilt indicator is available

General Specifications

Antenna Type Sector

Band Single band

Color Light Gray (RAL 7035)

Grounding TypeRF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

 Radiator Material
 Aluminum

 Reflector Material
 Aluminum

 RF Connector Interface
 4 3-10 Female

RF Connector Location Bottom

RF Connector Quantity, low band 4
RF Connector Quantity, total 4

Remote Electrical Tilt (RET) Information

RET Hardware CommRET v2

RET Interface 2x 8 pin connector as per IEC 60130-9 Daisy chain in: Male / Daisy chain out:

Female Pin3: RS485A(AISG_B), Pin5: RS485B(AISG_A), Pin6: DC 10~30V, Pin7:

DC_Return

RET Interface, quantity 1 female | 1 male

Input Voltage10-30 VdcInternal RETLow band (2)

Power Consumption, active state, maximum 10 W Power Consumption, idle state, maximum 2 W

Protocol 3GPP/AISG 2.0

Dimensions

COMMSC PE®


Width 467 mm | 18.386 in

Depth 167 mm | 6.575 in

Length 1997 mm | 78.622 in

Net Weight, antenna only 24.5 kg | 54.013 lb

Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG RET UID
R1	694-960	1 - 2	1	CPxxxxxxxxxxxxxxxxxX1
R2	694-960	3 - 4	2	CPxxxxxxxxxxxxxxxxR2

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications



Impedance 50 ohm

Operating Frequency Band 694 – 960 MHz

Polarization ±45°

Total Input Power, maximum 800 W

Electrical Specifications

Frequency Band, MHz	694-790	790-890	890-960
Gain, dBi	15.4	15.5	16.1
Beamwidth, Horizontal, degrees	66	64	66
Beamwidth, Vertical, degrees	11.2	9.7	9
Beam Tilt, degrees	0-10	0-10	0-10
USLS (First Lobe), dB	17	17	18
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	27	28	27
Isolation, Cross Polarization, dB	26	26	26
Isolation, Inter-band, dB	26	26	26
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150
Input Power per Port, maximum, watts	300	300	300

Electrical Specifications, BASTA

Frequency Band, MHz	694-790	790-890	890-960
Gain by all Beam Tilts, average, dBi	15	15.3	15.8
Gain by all Beam Tilts Tolerance, dB	±0.7	±0.3	±0.2
Beamwidth, Horizontal Tolerance, degrees	±3.6	±4.2	±4.4
Beamwidth, Vertical Tolerance, degrees	±0.9	±0.5	±0.5
Front-to-Back Total Power at 180° ± 30°, dB	22	23	23
CPR at Boresight, dB	25	25	25
CPR at Sector, dB	12	10	11

Mechanical Specifications

 Wind Loading @ Velocity, frontal
 820.0 N @ 150 km/h (184.3 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 308.0 N @ 150 km/h (69.2 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights



 Width, packed
 562 mm | 22.126 in

 Depth, packed
 287 mm | 11.299 in

 Length, packed
 2197 mm | 86.496 in

 Weight, gross
 36 kg | 79.366 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

BSAMNT-B95-03 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

