

CNT-300A-LB

CNT-300, CNT® 50 Ohm Low Braided Coverage Coaxial Cable, black non-halogenated jacket



Product Classification

Product Type	Braided coaxial cable
Product Brand	CNT®
Product Series	CNT-300

General Specifications

Braid Coverage	60 %
Cable Type	CNT-300
Jacket Color	Black

Dimensions

Diameter Over Dielectric	4.83 mm 0.19 in
Diameter Over Jacket	7.62 mm 0.3 in
Diameter Over Tape	5.003 mm 0.197 in
Inner Conductor OD	1.78 mm 0.07 in
Nominal Size	0.300 in

Electrical Specifications

Cable Impedance	50 ohm
Capacitance	80.4 pF/m 24.506 pF/ft
dc Resistance, Inner Conductor	11.05 ohms/km 3.368 ohms/kft
dc Resistance, Outer Conductor	14.95 ohms/km 4.557 ohms/kft
dc Test Voltage	2500 V
Jacket Spark Test Voltage (rms)	3500 V
Maximum Frequency	24.5 GHz

CNT-300A-LB

Operating Frequency Band	30 – 6000 MHz
Peak Power	10 kW
Shielding Effectiveness	85 dB
Velocity	83 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30.0	3.8	1.16
50.0	4.9	1.5
150.0	7.9	2.4
220.0	9.5	2.9
450.0	13.1	4
900.0	19.4	5.9
1500.0	25.3	7.7
1800.0	28.2	8.6
2000.0	29.8	9.1
2500.0	33.8	10.3
3000.0	37.4	11.4

Material Specifications

Braid Material	Tinned copper
Dielectric Material	Foam PE
Jacket Material	Non-halogenated PE
Inner Conductor Material	Copper-clad aluminum wire
Shield Tape Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, single Bend	22.352 mm 0.88 in
Tensile Strength	20 kg 44.092 lb
Bending Moment	0.3 N-m 2.655 in lb
Flat Plate Crush Strength	0.5 kg/mm 27.999 lb/in

Environmental Specifications

Installation temperature	-40 °C to +85 °C (-40 °F to +185 °F)
---------------------------------	--------------------------------------

CNT-300A-LB

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature -70 °C to +85 °C (-94 °F to +185 °F)

Packaging and Weights

Cable weight 0.05 kg/m | 0.034 lb/ft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system