

## N-Type Female High Power Termination Load, 70–3000 MHz

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Termination Load


### General Specifications

<b>Device Type</b>	Termination Load
<b>Color</b>	Silver
<b>Interface</b>	N Female

### Electrical Specifications

<b>Return Loss, minimum</b>	20 dB
<b>Average Power, maximum</b>	175 W
<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	70 – 3000 MHz
<b>Peak Power, maximum</b>	1.5 kW
<b>VSWR</b>	1.22

### Derating Curve



## Environmental Specifications

<b>Operating Temperature</b>	-33 °C to +65 °C (-27.4 °F to +149 °F)
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP30

## Packaging and Weights

<b>Height, packed</b>	242 mm   9.528 in
<b>Width, packed</b>	165 mm   6.496 in
<b>Length, packed</b>	130 mm   5.118 in
<b>Weight, gross</b>	3.7 kg   8.157 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

