EW180, HELIAX® Standard Elliptical Waveguide, 17.3–18.4 GHz, black PE jacket



Product Type		Standard elliptical waveguide			
Product Brand		HELIAX®			
Product Series		Standard			
General Specifications					
Jacket Color		Black			
Performance Note		Values typical, unless otherwi	se stated		
Dimensions					
Diameter Over Jacket (E Plane)		20.1 mm 0.791 in			
Diameter Over Jacket (H Plane)		12.4 mm 0.488 in			
Cable Volume		111 L/km 1.195 ft ³ /kft			
Electrical Specifications					
eTE11 Mode Cutoff		11.15 GHz			
Group Delay at Frequency		127 ns/100 ft @ 18.700 GHz 416 ns/100 m @ 18.700 GHz			
Operating Frequency Band		17.3 – 18.4 GHz			
VSWR/Return Loss					
Frequency Band	VSWR	Return Loss (dB)			
17.3-18.4 GHz	1.15	23.13			
Attenuation					
Frequency (GHz)	Attenuation (dB/100 m) Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %	
17.3	20.468	6.239	0.528	76.5	

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

COMMSCOPE°

EW180-173

17.7	20.111	6.13	0.537	77.7		
18.1	19.799	6.035	0.546	78.8		
Material Specifications						
Conductor Material		Corrugated copper				
Jacket Material		PE				
Mechanical Specifications						
Minimum Bend Radius, Multiple Bends (E Plane)		150 mm 5.906 in				
Minimum Bend Radius, Multiple Bends (H Plane)		380 mm 14.961 in				
Minimum Bend Radius, Single Bend (E Plane)		150 mm 5.906 in				
Minimum Bend Radius, Single Bend (H Plane)		380 mm 14.961 in				
Maximum Twist		6.562 °/m 2 °/ft				
Environmental Spe	ecifications					
Installation temperature		-40 °C to +60 °C (-40 °F to +140 °F)				
Operating Temperature		-55 °C to +85 °C (-67 °F to +185 °F)				
Storage Temperature		-70 °C to +85 °C (-94 °F to +185 °F)				
Attenuation, Ambient Temperature		75 °F 23.889 °C				
Average Power, Ambient Temperature		104 °F 40 °C				
Average Power, Temperature Rise		42 °C 107.6 °F				
Packaging and Weights						
Cable weight		0.22 kg/m 0.148 lb/ft				

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

COMMSCOPE°