

# PULSAR-EDGE-C2

---



PowerShift® High Power Pulsar Edge Controller with C2 software  
(included with shelf)

## Product Classification

<b>Product Type</b>	Module
<b>Product Brand</b>	PowerShift®
<b>Product Series</b>	V2

## General Specifications

<b>Backplane Interfaces</b>	10/100 Base-T Ethernet   One Galaxy Protocol (GP) RS485 bus
<b>Front Panel Display</b>	Interface to shelf mounted interactive display

## Dimensions

<b>Height</b>	41.402 mm   1.63 in
<b>Width</b>	18.288 mm   0.72 in
<b>Depth</b>	345.44 mm   13.6 in

## Electrical Specifications

<b>Electrical Safety Standard</b>	UL60950-UL/cUL with CB report
-----------------------------------	-------------------------------

## Environmental Specifications

<b>Relative Humidity</b>	95%, non-condensing
<b>Ambient Temperature</b>	-40 °C   -40 °F   65 °C   149 °F
<b>Mean Time Between Failures (MTBF) at Temperature</b>	300,000 h @ 25 °C

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# PULSAR-EDGE-C2

---

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

