EW132, HELIAX® Standard Elliptical Waveguide, 14.4–15.35 GHz, black PE jacket



Product Type		Standard elliptical waveguide		
Product Brand		HELIAX®		
Product Series		Standard		
General Specifications				
Jacket Color		Black		
Performance Note		Values typical, unless otherwi	se stated	
Dimensions				
Diameter Over Jacket (E Plane)		24.4 mm   0.961 in		
Diameter Over Jacket (H Plane)		15.5 mm   0.61 in		
Cable Volume		167 L/km   1.798 ft <sup>3</sup> /kft		
Electrical Specifications				
eTE11 Mode Cutoff		9.22 GHz		
Group Delay at Frequency		131 ns/100 ft @ 14.700 GHz	428 ns/100 m @ 14.	700 GHz
Operating Frequency Band		14.4 – 15.35 GHz		
VSWR/Return Loss				
Frequency Band	VSWR	Return Loss (dB)		
14.4-15.35 GHz	1.15	23.13		
Attenuation				
Frequency (GHz)	Attenuation (dB/100 m	) Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %

4.882

0.843

14.4

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

16.018



76.8

# EW132-144

14.6	15.874	4.838	0.85	77.5
14.8	15.74	4.798	0.858	78.2
15.0	15.616	4.76	0.865	78.9
15.2	15.501	4.725	0.871	79.5

# Material Specifications

#### **Conductor Material**

**Jacket Material** 

ΡE

Corrugated copper

# Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	130 mm   5.118 in
Minimum Bend Radius, Multiple Bends (H Plane)	360 mm   14.173 in
Minimum Bend Radius, Single Bend (E Plane)	130 mm   5.118 in
Minimum Bend Radius, Single Bend (H Plane)	360 mm   14.173 in
Maximum Twist	6.562 °/m   2 °/ft

### **Environmental Specifications**

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
Attenuation, Ambient Temperature	75°F   23.889°C
Average Power, Ambient Temperature	104 °F   40 °C
Average Power, Temperature Rise	42 °C   107.6 °F

## Packaging and Weights

#### Cable weight

0.33 kg/m | 0.222 lb/ft

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023



EW132-144



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

