

# EW220

EW220, HELIAX® Standard Elliptical Waveguide, 21.2–23.6 GHz, black PE jacket



## Product Classification

<b>Product Type</b>	Standard elliptical waveguide
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	Standard

## General Specifications

<b>Jacket Color</b>	Black
<b>Performance Note</b>	Values typical, unless otherwise stated

## Dimensions

<b>Diameter Over Jacket (E Plane)</b>	17.8 mm   0.701 in
<b>Diameter Over Jacket (H Plane)</b>	11.2 mm   0.441 in
<b>Cable Volume</b>	74 L/km   0.797 ft³/kft

## Electrical Specifications

<b>eTE11 Mode Cutoff</b>	13.338 GHz
<b>Group Delay at Frequency</b>	127 ns/100 ft @ 22.400 GHz   415 ns/100 m @ 22.400 GHz
<b>Operating Frequency Band</b>	21.2 – 23.6 GHz

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
21.2–23.6 GHz	1.15	23.13

## Attenuation

Frequency (GHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
21.2	28.042	8.547	0.398	77.7

# EW220

21.6	27.799	8.473	0.401	78.7
22.0	27.577	8.406	0.404	79.5
22.4	27.376	8.344	0.407	80.3
22.8	27.192	8.288	0.41	81.1
23.2	27.024	8.237	0.413	81.8
23.6	26.87	8.19	0.415	82.5

## Material Specifications

<b>Conductor Material</b>	Corrugated copper
<b>Jacket Material</b>	PE

## Mechanical Specifications

<b>Minimum Bend Radius, Multiple Bends (E Plane)</b>	120 mm   4.724 in
<b>Minimum Bend Radius, Multiple Bends (H Plane)</b>	230 mm   9.055 in
<b>Minimum Bend Radius, Single Bend (E Plane)</b>	120 mm   4.724 in
<b>Minimum Bend Radius, Single Bend (H Plane)</b>	230 mm   9.055 in
<b>Maximum Twist</b>	6.562 °/m   2 °/ft

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	75 °F   23.889 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Temperature Rise</b>	42 °C   107.6 °F

## Packaging and Weights

<b>Cable weight</b>	0.18 kg/m   0.121 lb/ft
---------------------	-------------------------

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

# EW220

---

UK-ROHS

Compliant

