

760239072 | UDS-6U-BK-LA-B



UDS 6RU splice panel, 432 duplex LC/APC ports, Enhanced Method B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	UDS

General Specifications

Application	Preloaded with 36 UDS modules
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	LC/APC
Pigtail Assembly Type	12-fiber, ribbon
Pigtails Included, quantity	36
Rack Type	EIA 19 in
Rack Units	6
Shelf Movement	Sliding
Splice Trays Included, quantity	12
Total Ports, quantity	432

Dimensions

Height	266.7 mm 10.5 in
Width	444.5 mm 17.5 in
Depth	609.6 mm 24 in

Optical Specifications

760239072 | UDS-6U-BK-LA-B

Insertion Loss, maximum 0.4 dB

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Weight, net 20.412 kg | 45 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

