

# CA9927-000 | OCM1-CMI471S2



OCM1 LGX Fiber Optic Module, CWDM, Mux, SC/APC, 2 channels, upgrade port, 1310 nm port, starting wavelength 1470 nm

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	CWDM module
<b>Product Series</b>	LGX   OCM1

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Multiplexing
<b>Technology Type</b>	Thin film filter (TFF)
<b>Application</b>	For use with LGX panels
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	2-channel CWDM
<b>Interface, front</b>	SC/APC
<b>Interface, Input</b>	SC/APC
<b>Interface, Output</b>	SC/APC
<b>Multiplexers, quantity</b>	1
<b>Port Type, optional</b>	1310 nm port   Upgrade port

## Dimensions

<b>Height</b>	129.54 mm   5.1 in
<b>Width</b>	27.94 mm   1.1 in
<b>Depth</b>	127 mm   5 in

## Optical Specifications

<b>Channel Spacing</b>	20 nm
<b>Starting Wavelength</b>	1470 nm

## Packaging and Weights

**Packaging quantity** 1  
**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

