



Butyl Rubber Tape, 24 in

Product Classification

| | |
|----------------------|---------------------------------|
| Product Type | Weatherproofing tape |
| Ordering Note | CommScope® non-standard product |

General Specifications

| | |
|-----------------------------|---|
| Application | Provides additional moisture seal for cable connections |
| Applications per Kit | One 1/2 in–2-1/4 in One 1/2 in–7/8 in One 1/2 in–7/8 in to device Two 1/2 in–1/2 in |
| Color | Black |

Dimensions

| | |
|---------------------|---|
| Width | 63.5 mm 2.5 in |
| Length | 609.6 mm 24 in |
| Nominal Size | 1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7/8 in |

Material Specifications

| | |
|----------------------|-------------------|
| Material Type | Butyl rubber tape |
|----------------------|-------------------|

Environmental Specifications

| | |
|---|---|
| UV Resistance Test Method | Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4 hours of condensation at 104 °F |
| UV Resistance, minimum with no degradation | ≥1000 hours |
| Weather Resistance Test Method | 04AS00-03.6.0 MIL-STD-1344A, Method 1002 |

Packaging and Weights

| | |
|-----------------------|-------------------|
| Height, packed | 63.5 mm 2.5 in |
| Width, packed | 71.12 mm 2.8 in |
| Length, packed | 25.4 mm 1 in |

42615-10

Packaging quantity 1
Weight, gross 0.17 kg | 0.375 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |