

# FPX-12MPRDA9



FPX Fiber Optic MPO Module, Multimode Ultra 50/125 (OM3), 12 fiber SC adapter, right, putty white

- FPX modules offer the end-user the flexibility of a plug-and-play MPO architecture with a “grow as you go” approach to the network
- Each module has a front bulkhead identical to the adapter pack with an internal cable assembly converting to an MPO male connector
- All fiber connectivity is housed in an enclosed module with a rear MPO adapter allowing the user to utilize an MPO trunk to turn up service

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Series</b>	FPX

## General Specifications

<b>Functionality</b>	Breakout
<b>Application</b>	For use with FPX panels
<b>Adapters, quantity, front</b>	12
<b>Adapters, quantity, rear</b>	1
<b>Body Style</b>	Right orientation   Simplex
<b>Color, front</b>	Putty white
<b>Color, housing</b>	Putty white
<b>Color, rear</b>	Putty white
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Standard
<b>Polarity</b>	Pairs, straight
<b>Total Ports, quantity, front</b>	12


## Dimensions

<b>Height</b>	33.02 mm   1.3 in
<b>Width</b>	176.53 mm   6.95 in

# FPX-12MPRDA9

**Depth** 127 mm | 5 in

## Ordering Tree



<sup>1</sup> SC only

<sup>2</sup> LC only

## Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM3

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

# FPX-12MPRDA9

---

TL 9000:2016 (R6)

Compliant to this quality management practice

UK-ROHS

Compliant

