

UFVLULUK2

Base Product



Ultra Low Loss OM5, LC/UPC Uniboot to LC/UPC Uniboot, 1.5 mm Duplex Fiber Patch Cord, Low Smoke Zero Halogen/Riser

- Patch cords using Uniboot technology combine, modularity, flexibility with easy insertion and removal from connectivity
- Uniboot connectors feature an adjustable polarity via a manual and independent rotation of each single connector body without exposing the fibers
- Uniboot technology features a push-pull mechanism operated by squeezing the connector boot
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East /Africa | North America

Portfolio

CommScope®

Product Type

Fiber patch cord, duplex

Product Brand

SYSTIMAX ULL

Product Series

UFV

Government Funding

Build America Buy America (BABA) compliant*

Ordering Note

For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, connector A

Beige

Color, connector B

Beige

Interface, Connector A

LC/UPC

Interface Feature, connector A

Uniboot

Interface, Connector B

LC/UPC

Interface Feature, connector B

Uniboot

Jacket Color

Lime green

Total Fibers, quantity

2

UFVLULUK2



Included Products

- 760251281 N-002-DU-5G-M15LM/AY/LTS – Fiber Indoor Cable, LazrSPEED® Low Smoke Zero Halogen Light Duty Interconnect, 2 fiber, Multimode OM5, Gel-free, Meters jacket marking, Lime green jacket color