

In-Line MPO Adapter Housing

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter enclosure
Ordering Note	Minimum length may vary based on cable configuration

General Specifications

Application	Additional protection when mating an InstaPATCH® Plus trunk cable to an InstaPATCH® Plus extension cable or ruggedized fanout
Interface	MPO

Dimensions

Compatible Cable Diameter	3 mm 0.118 in
----------------------------------	-----------------

Mechanical Specifications

Tensile Load, maximum	48.93 N 11 lbf
------------------------------	------------------

Packaging and Weights

Included	Hook and loop fastener Housing Label Two MPO adapters
-----------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

