MR3919-000 | FDSC-GATOR-12F-T



Gator 12F Fiber Optic Splice Closure, Re-enterable, Gel Cable sealing, for up to 12 splices

- Designed for splicing two loose tube "flat drop" style cables of 1 to 12 fibers in above grade, below grade, and direct buried applications
- Uses gel sealing technology to create a sealed closure system that will fit into confined areas such as small "flowerpot" style handholes
- Incorporates our unique cable hold down and strength member termination features and is capable of holding either fusion or mechanical splices
- Tone wires can also be terminated outside of the closure using the included hardware

Product Classification

Regional Availability	Latin America North America
Product Type	Single-ended, flat fiber closure
Product Series	FDSC GATOR
General Specifications	
Cable Entry Drop Port Style	Flat
Cable Entry Main Port Style	Flat
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Wall
Network Area Type	Drop
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, Single Fusion, maximum	12
Splicing Type, Supported	Mass fusion Single fusion
Dimensions	
Height	30.48 mm 1.2 in
Width	147.32 mm 5.8 in
Length	190.5 mm 7.5 in

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 16, 2024



MR3919-000 | FDSC-GATOR-12F-T

Environmental Specifications

Environmental Space		Below ground Buried	
Packaging and Weights			
Packaging quantity		10	
Packaging Type		Box Carton	
Regulatory Compliance/Certifications			
Agency	Classification		
CHINA-ROHS	Below maximum concentration value		
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system		
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance		
ROHS	Compliant		
UK-ROHS	Compliant		

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 16, 2024

