

### Installation Guidelines – HELIAX® FiberFeed® Direct

### Solution: 6x6, 6x12 Multimode Configurations

#### Related Support and Learning Opportunities Offered by the CommScope Infrastructure Academy

The insights and expertise contained in this manual represent just one small part of Andrew Solutions global learning initiative. Few industries are evolving as quickly as wireless communications. Every technological innovation impacts what happens in the field. Our customers look to the CommScope Infrastructure Academy to make sure their technicians and installers are well trained, well-prepared, and well-educated to take advantage of opportunities as they evolve. To access a course, go to www.commscopetraining.com/coursecatalog.php, course #6107

### Field Engineering Services (FES)

Support services, such as our Field Engineering Services (FES) Group gives Andrew Solutions' customers access to technical support where and when it is needed the most — in the field. The FES team is staffed by an expert team of technicians who, in turn, are supported by some of the brightest and most experienced product line managers. With all of this knowledge and support the FES offers our customers access to hands-on, specialized training classes.

Section 1: Direct Configurations	02
Section 2: HELIAX® FiberFeed® Direct Components / Accessories	03
Section 3: DCM-U-V2 Mounting	04
Section 4: General Specifications	05
Section 5: Hoisting Considerations	06
Section 6: General Specifications Tails	08
Section 7: Outdoor DLC Connection Procedure	09
Section 8: Supporting Fiber Tails / Supporting Future Expansion Tails	10
Section 9: Breakout Procedure / DLC Connection Considerations	11
Section 10: All-in-One Cleaner / Inspecting	12
Section 11: Excess Cable Management	13
Section 12: Jacketing Removal Procedure / Installation Check List	14





#### For more information. Contact Customer Service Center

United States and Mexico 1-800-255-1479 or 1-888-235-5732 International: +1-779-435-8579

For the most current, up-to-date information on all our products and product information please visit our eCatalog section at www.commscope.com/andrew.










## **HELIAX®** FiberFeed® Direct Components



## **Accessories**





WARNING: CommScope Hybrid FiberFeed cables require the use of approved installation accessories.


	Cable Series	Part Number	Description
	FDH610	FA-1923-STH	Standard Hanger
		FA-2021-SIH	Snap-In Hanger
	FDH608	42396A-5	Standard Hanger
		FA-2628-SIH	Snap-In Hanger
	FDH606	42396A-5	Standard Hanger
		252115	Snap-In Hanger
	FDH1210	42396A-9	Standard Hanger
		FA-2628-SIH	Snap-In Hanger
	FDH1208/1206	FA-3236-STH	Standard Hanger
	DFJ	42396A-5	Standard Hanger
		SSH-12	Snap-In Hanger
		HG-5MM-12	Grommet
	All FDH series	243684	Angle Adapter, compact 3/8 in tapped hole
79	All FDH series	19256B-C	Hoisting Grip (lace-up)



## DCM-U-V2 Mounting









General Specifications  Cable Type	FDH1206-12M50-XXX	ED113000 1014E0 VVV	FDH1210-12M50-XXX
Brand		FDH1208-12M50-XXX	
Center Conductor Gauge	HELIAX® FiberFeed®  6 AWG	HELIAX® FiberFeed®	HELIAX® FiberFeed®
Conductors, quantity	6 AWG	8 AWG	10 AWG
, ,		6	6
Total Fiber Quantity	12	12	12
Shielding Type	Corrugated aluminum	Corrugated aluminum	Corrugated aluminum
Fiber Type	Multimode fiber	Multimode fiber	Multimode fiber
Construction Type	Direct Breakout	Direct Breakout	Direct Breakout
Dimensions			
Cable Weight	2421.0 kg/km   1627.0 lb/kft	1752.0 kg/km   1177.0 lb/kft	1050.0 kg/km   705.5 lb/kft
Diameter Over Jacket	36.20 mm   1.43 in	33.10 mm   1.30 in	25.14 mm   0.99 in
Breakout Length, Fiber, end 1	900 mm, 750 mm, 600 mm 35 in, 29in, 24in	900 mm, 750 mm, 600 mm 35 in, 29in, 24in	900 mm, 750 mm, 600 mm 35 in, 29in, 24in
Breakout Length, Power, end 1	5000 mm   197 in	5000 mm   197 in	5000 mm   197 in
Breakout Length, Fiber, end 2	1200 mm, 1150 mm, 1100 mm	1200 mm, 1150 mm, 1100 mm	1200 mm, 1150 mm, 1100 mm
<u> </u>	47 in, 45 in, 43 in	47 in, 45 in, 43 in	47 in, 45 in, 43 in
Breakout Length, Power, end 2	1000 mm   39 in	1000 mm   39 in	1000 mm   39 in
Physical Specifications			
Minimum Bend Radius, loaded	723.9 mm   28.5 in	662.9 mm   26.1 in	502.9 mm   19.8 in
Minimum Bend Radius, unloaded	363.2 mm   14.3 in	330.2 mm   13.0 in	251.5 mm   9.9 in
Tensile Load, long term, maximum	2002 N   450 lbf	2002 N   450 lbf	1068 N   240 lbf
Tensile Load, short term, maximum	6672 N   1500 lbf	6672 N   1500 lbf	3559 N   800 lbf
General Specifications			
Cable Type	FDH1206-24M50-XXX	FDH1208-24M50-XXX	FDH1210-24M50-XXX
Brand	HELIAX® FiberFeed®	HELIAX® FiberFeed®	HELIAX® FiberFeed®
Center Conductor Gauge	6 AWG	8 AWG	10 AWG
Conductors, quantity	6	6	6
Total Fiber Quantity	24	24	24
Shielding Type	Corrugated aluminum	Corrugated aluminum	Corrugated aluminum
Fiber Type	Multimode fiber	Multimode fiber	Multimode fiber
Construction Type	Direct Breakout	Direct Breakout	Direct Breakout
Dimensions			
Cable Weight	2421.0 kg/km   1627.0 lb/kft	1752.0 kg/km   1177.0 lb/kft	1050.0 kg/km   705.5 lb/kft
Diameter Over Jacket	36.20 mm   1.43 in	33.10 mm   1.30 in	25.14 mm   0.99 in
Breakout Length, Fiber, end 1	900 mm, 750 mm, 600 mm 35 in, 29in, 24in	900 mm, 750 mm, 600 mm 35 in, 29in, 24in	900 mm, 750 mm, 600 mm 35 in, 29in, 24in
Breakout Length, Power, end 1	5000 mm   197 in	5000 mm   197 in	5000 mm   197 in
Breakout Length, Fiber, end 2	1200 mm, 1150 mm, 1100 mm	1200 mm, 1150 mm, 1100 mm	1200 mm, 1150 mm, 1100 mm
STOCKOOT LOTIGITI, FIDOL, GIIG Z	47 in, 45 in, 43 in	47 in, 45 in, 43 in	47 in, 45 in, 43 in
	1000 mm   39 in	1000 mm   39 in	1000 mm   39 in
Breakout Length, Power, end 2			I
Physical Specifications	723.9 mm   28.5 in	662.9 mm   26.1 in	502.9 mm   19.8 in
Physical Specifications  Minimum Bend Radius, loaded	723.9 mm   28.5 in 363.2 mm   14.3 in	662.9 mm   26.1 in	502.9 mm   19.8 in
Physical Specifications  Minimum Bend Radius, loaded  Minimum Bend Radius, unloaded	363.2 mm   14.3 in	330.2 mm   13.0 in	251.5 mm   9.9 in
Physical Specifications  Minimum Bend Radius, loaded	· ·	•	· ·




### **Hoisting Considerations**

- In general this cable will handle similarly to coaxial cable, and similar installation techniques apply. All cables are individually serialized, be sure to write down the cable serial number for future reference.
- Leave the protective sock around the fiber tails and power conductors during hoisting and securing the cable.
- Be sure that the Direct breakout is not damaged by attachment of a hoisting grip or during the hoisting process. Attach a hoisting grip on the jacketed cable no less than .3 m (1 ft) below the fiber breakout point. Prevent the fiber tails and power conductors from undue movement during hoisting by securing the protective sock with tie ropes every 1 m (3 ft) to the hoisting line.
- During hoisting ensure that there is a free path and that the cable, and especially the end of the pulling sock will not be snagged on tower members or other obstacles.
- Installation temperature range is -22 F to +158 F (-30 C to +70 C).
- Minimum cable bend radii can be found on-line in our eCatalog section at www.commscope.com/andrew.
- Maximum cable tensile load can be found on-line in our eCatalog section at www.commscope.com/andrew.
- CommScope Lace-Up Hoisting Grip 19256B-C required for FDH-series installations.
- Hoisting Grip should be anchored to the support structure after the hangers are installed.
- During final connections to RRU, do not bend the fiber ends tighter than 30 MM (1.2 IN) bend radius or you take the risk of breaking the glass fibers.

 $\triangle$ 


Hybrid Fiber Cables weigh more than traditional coaxial cables. Be sure to follow proper hoisting and attachment procedures.

## **Hoisting Recommendations**



Reminder: Plan grip location by measuring distance (D) from Outdoor DLC connector to tower support member.







### **General Specifications Tails**


- In general this cable will handle similarly to coaxial cable.
- The terminated fiber ends however are fragile and must be protected during installation. Leave the packaging around the fiber ends in place until ready to make final connection of the jumper at the RRU or BBU.
- DO NOT BEND THE FIBER ENDS TIGHTER THAN 1.2" (30mm) BEND RADIUS ELSE THERE IS A RISK OF BREAKING THE GLASS FIBERS.
- Attach the main cable securely to the structure or equipment using hangers to prevent strain on connections from
  movement in wind or snow/ice conditions.
- Ensure the DLC fiber connector is seated firmly in RRU.
- DLC outdoor connector is a 1/4 turn and will have an audible click when fully engaged.
- Ensure the weatherproof boots for both fiber and power connections are seated firmly in the RRU.
- Installation temperature range is -22F to 158F (-30C to 70C).
- All tails are individually serialized, for immediate access to test results visit www.commscope.com/webtrak/

			RRU
General Specifications		<u> </u>	
Cable Type	DFJ-2M-10x-xxM		DLC
Brand	HELIAX® FiberFeed®		connector
Total Fiber Quantity	2		
Fiber Type	Multimode fiber	i i	
Jacket Color	Black		
Dimensions			
Cable Weight	37.1 kg/km   24.9 lb/kft		
Diameter Over Jacket	6 mm   .24 in		
Physical Specifications		Cable	
Minimum Bend Radius, loaded	9 cm   3.5 in	Assembly	
Minimum Bend Radius, unloaded	6 cm   2.4 in	Length ``·'	
Tensile Load, long term, maximum	334 N   75 lbf		Multimode
Tensile Load, short term, maximum	1110 N   250 lbf	-	fiber cable
		DFJ-2M100-xxM	Outdoor DLC connector with adapter
		(shown)	End 2 Direct Breakout

End 1




## **Outdoor DLC connection procedure**






## Supporting Fiber Tails (Power tails require standard hangers)


1. Open grommet and place it over the fiber tail.



2. Place the hanger over the grommet and place in support structure.




**3.** Stack hangers as required. Repeat with tails being routed to the RRU and spare fibers.



Connectors are fully weather sealed and do not require additional weatherizing. Unused power conductors should be left with the protective cap in place.


Maximum hanger spacing of 0.9m (3 ft) - 1.2m (4 ft)



## Optional:

- 1. If additional hangers are not available slide the BBU end protection sleeve back over any spare fibers to protect them.
- 2. Place tape over fiber tails and protective sleeve end to hold in place. Support protection sleeve using tie wraps.







#### **Breakout Procedure**

After the trunk cable has been installed and you are ready to make the final connection to the RRU or BBU follow these steps for the removal of fiber protection tube.



Remove electrical tape from the trunk cable and corrugated protection tube

2



While holding the protection tube straight pull the tube away from cable.






After you have pulled the fiber and power conductors into the OVP box remove electrical tape from the trunk cable and remove clear tube for access to all optical connectors.

### **DLC Connectors and Adapter cleaning**

Clean exposed connector ferrule by lightly moistening lint-free wipe with fiber optic cleaning solution (or >91% isopropyl alcohol), and by applying medium pressure, first wipe against wet area and then onto dry area to clean potential residue from end face. Clean connector ferrule inside adapter by inserting lightly moistened cleaning stick with fiber optic cleaning solution (or >91% isopropyl alcohol) inside the adapter until contact is made with connector on opposite end. Rotate cleaning stick with medium pressure in one circular motion as it is pulled away from the adapter. Repeat process using dry cleaning stick.

**Caution:** Signal strength will be affected if end and sides of ferrule are not thoroughly cleaned. Discard cleaning sticks after each use. Do not turn cleaning sticks back and forth pressing against connector end face. This may cause scratches if large contamination is present. Always inspect connector end face for contamination after each cleaning.



Clean adapter by inserting adapter cleaning stick (or fiber adapter sleeve brush) moistened with fiber optic cleaning solution (or >91% isopropyl alcohol) inside the adapter and gently pull out with twisting motion. Repeat process with a dry cleaning stick.

**Caution:** Do not try to clean adapter with a standard pipe cleaner. The sleeve inner diameter of DLC adapters is too small. Do not try to clean the adapter with cleaning stick if a connector is mounted in one side. Discard cleaning sticks after each use.

Adapter Brush




#### All in one cleaner

Device designed for cleaning the ferrule end faces of LC connectors

Open guide cap, insert LC connector into guide, push the outer shell to start cleaning the LC connector interface, a "click" sound indicates end of a cleaning process, repeat, close cap immediately after use.

**Caution:** Be careful not to slant LC connector while inserting into the Guide cap. Do not overly exert force during insertion as this may cause damage to both the connector and the cleaner.



### Inspecting

There are 3 basic principles that are critical to achieving an efficient fiber optic connection:




Scan to view video

- 1. Perfect Core Alignment
- 2. Physical Contact
- 3. Pristine Connector Interface

Today's connector design and production techniques have eliminated most of the challenges to achieving core alignment and physical contact. What remains challenging is maintaining a pristine end-face. As a result, CONTAMINATION is the #1 reason for troubleshooting optical networks.

Implementing the process of cleaning and inspecting before mating can reduce the time spent troubleshooting, optimize signal performance and prevent damage.





## **Excess Cable Management**

If length of cable installed needs to be adjusted you can split the cable at the BBU end using the process below and then coiling the excess fiber subunits in a storage box. Patch Panel Kits are available to manage any excess fiber length in the breakouts at the BBU.

Mark cutback length



Notch Armor using flush cutter in-line with Kevlar strings





Excess Fiber storage Box Part Number: FE-14126-E

3 Place Rip Cord in Notches



Pull Rip Cord Parallel to Cable (while supporting breakout)





Fiber management tray, Part Number: FE-14192-IR

5 Stop at Length Marker



6 Separate Armor



Cable Splitter tool Part Number: FA-RCRT-PD

7 Cut Armor Using Side Cutter

Remove Excess Rip Cord



8 Remove Water Blocking Tape



Step can be expedited by using a sewing seam ripper that can be purchased at local hobby stores



Seam Ripper



Apply Electrical Tape to Protect Breakout



NOTE:

Remember to slide identifier labels down the power conductors before trimming the cable to its final length





Scan to view video



Click here to view video



### Jacketing Removal Procedure for Grounding Kit Installation

- 1. Score the jacketing 360°
- 2. Measure 2" (51 mm) and repeat
- 3. Identify where the aluminum shielding overlaps, this will feel like a flat spot in the cable
- 4. With a knife flat on the cable remove a section of jacketing between score marks
- 5. Lift edge of jacketing with knife tip
- 6. Grab lifted edge of jacketing with a pair of pliers and roll on the cable
- 7. Remove excess adhesive with a piece of emery cloth







Scan to view video

Click here for video

#### **Installation Check List**

Tails are properly supported to prevent strain on fiber during severe weather
Bend radius minimums haven't been exceeded
CommScope approved installation accessories are used
Maximum hanger spacing of 0.9m (3 ft) - 1.2m (4 ft) is maintained
Visually inspected end face for residual dirt and damage
Avoid migration of contaminations from one connector to another
Check continuity by using LED or laser light source from one end face and look for light from other end to identify any broken fiber (Do not look directly at cable with laser source)
Fiber Connections are engaged and the sectors are consistent with requirements
Cable serial number has been documented in the closeout paperwork and a copy has been left on-site

#### CommScope

1100 CommScope Place SE P.O. Box 339, Hickory, NC 28603-0339 (828) 324-2200 (800) 982-1708 www.commscope.com/andrew

**Customer Service 24 hours** 

North America: +1-800-255-1479 (toll free)
Any country: +1-779-435-6500
email: acicustomersupportcenter@commscope.com

Notice: CommScope disclaims any liability or responsibility for the results of improper or unsafe installation, inspection, maintenance, or removal practices.

Aviso: CommScope no acepta ninguna obligación ni responsabilidad como resultado de prácticas incorrectas o peligrosas de instalación, inspección, mantenimiento o retiro.

Avis: CommScope décline toute responsabilité pour les conséquences de procédures d'installation, d'inspection, d'entretien ou de retrait incorrectes ou dangereuses.

Hinweis: CommScope lehnt jede Haftung oder Verantwortung für Schäden ab, die aufgrund unsachgemäßer Installation, Überprüfung, Wartung oder Demontage auftreten.

Atenção: A CommScope abdica do direito de toda responsabilidade pelos resultados de práticas inadequadas e sem segurança de instalação, inspeção, manutenção ou remoção.

Avvertenza: CommScope declina eventuali responsabilità derivanti dell'esecuzione di procedure di installazione, ispezione, manutenzione e smontaggio improprie o poco sicure.

注意:CommScope 公司申明對於不恰當或不安全的安裝、檢驗、維修或拆卸操作所導致的后果不負任 何義務和責任

© 2015 CommScope