

# CT-5-TUW-NI6



5 dB, Tapper, 340 – 6000 MHz

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Product Type</b>          | Tapper  |

## General Specifications

|                              |                |
|------------------------------|----------------|
| <b>Device Type</b>           | Tapper         |
| <b>Application</b>           | Indoor/Outdoor |
| <b>Color</b>                 | White          |
| <b>Inner Contact Plating</b> | Silver         |
| <b>Interface</b>             | N Female       |
| <b>Outer Contact Plating</b> | Trimetal       |

## Dimensions

|               |                   |
|---------------|-------------------|
| <b>Height</b> | 25 mm   0.984 in  |
| <b>Width</b>  | 43 mm   1.693 in  |
| <b>Length</b> | 141 mm   5.551 in |

## Electrical Specifications

|   |  |
|---|--|
| <b>3rd Order IMD</b>                    | -163 dBc   |
| <b>3rd Order IMD Test Method</b>        | Two +43 dBm carriers   |
| <b>Insertion Loss at Frequency Band</b> | 1.8 dB @ 340–960 MHz   1.95dB @ 3500-4500MHz   1.95dB @ 4900-6000MHz   2.1 dB @ 1695-2700MHz   |
| <b>Return Loss at Frequency Band</b>    | 16.5dB @ 3500–4500MHz   17.7 dB @ 4900–6000 MHz   17.7dB @ 340–960MHz   20.8 dB @ 1695–2700 MHz  |
| <b>Average Power, maximum</b>           | 300 W  |
| <b>Coupling</b>                         | 5 dB   |
| <b>Coupling Tolerance</b>               | +0.15/-0.6dB @ 698-960MHz   +0.2/-1.7dB @ 3500-4500MHz   +0.3/-0.8dB @ 4900-6000MHz   +0/-1.3dB @ 340-380 MHz   -0.2/-1.1dB @ 380-520 MHz   ±0.6dB @ 1695-2700 MHz |

# CT-5-TUW-NI6

---

|                                 |   |
|---------------------------------|---|
| <b>Impedance</b>                | 50 ohm  |
| <b>Operating Frequency Band</b> | 1695 – 2700 MHz   340 – 960 MHz   3500 – 4500 MHz   4900 – 6000 MHz |
| <b>Peak Power, maximum</b>      | 3 kW  |
| <b>Reflected Power, maximum</b> | 200 W   |

## Mechanical Specifications

|                                  |                        |
|----------------------------------|------------------------|
| <b>Coupling Nut Proof Torque</b> | 4.5 N-m   39.828 in lb |
|----------------------------------|------------------------|

## Environmental Specifications

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| <b>Operating Temperature</b>          | -35 °C to +85 °C (-31 °F to +185 °F) |
| <b>Relative Humidity</b>              | Up to 100%                           |
| <b>Ingress Protection Test Method</b> | IEC 60529:2001, IP67                 |

## Packaging and Weights

|                       |                   |
|-----------------------|-------------------|
| <b>Height, packed</b> | 40 mm   1.575 in  |
| <b>Width, packed</b>  | 90 mm   3.543 in  |
| <b>Length, packed</b> | 180 mm   7.087 in |
| <b>Weight, gross</b>  | 300 g   0.661 lb  |
| <b>Weight, net</b>    | 250 g   0.551 lb  |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

