

ATTEN-NMNF-15

Inline Attenuator, N-m/N-f, 15 dB



Product Classification

Product Type Coax attenuator

General Specifications

Connector Interface N Female | N Male

Outer Contact Plating Trimetal

Plating Nickel


Dimensions

Length 70 mm | 2.756 in

Diameter 16 mm | 0.63 in

ATTEN-NMNF-15

Outline Drawing



Electrical Specifications

Input Power, PEP, maximum	250 W
Input Power, RMS, maximum	2 W
Return Loss, minimum	20 dB
Attenuation	15 dB
Attenuation Tolerance	± 0.5 dB
Impedance	50 ohm
Operating Frequency Band	DC – 3000 MHz

Material Specifications

Dielectric Material	PTFE
Material Type	Brass
Inner Contact Plating	Gold

Environmental Specifications

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
------------------------------	--------------------------------------

ATTEN-NMNF-15

Packaging and Weights

Weight, net

77 g | 0.17 lb