

# LM-100-SSH



Tapered Pipe-to-Pipe Adapter, adapts 4 in to 9 in OD pipe to 8 in to 16 in OD pipe

## Product Classification

**Product Type** Adapter

## General Specifications

**Mounting** Pipe-to-pipe

**Taper Taper** Tapered

## Dimensions

**Height** 50.8 mm | 2 in  
**Width** 508 mm | 20 in  
**Length** 762 mm | 30 in  
**Mounting Diameter 2, maximum** 406.4 mm | 16 in  
**Mounting Diameter 2, minimum** 203.2 mm | 8 in  
**Mounting Diameter, maximum** 228.6 mm | 9 in  
**Mounting Diameter, minimum** 101.6 mm | 4 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamp halves | Threaded rod

**Packaging quantity** 2

**Weight, net** 29.9 kg | 65.918 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

### Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

# LM-100-SSH

---

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

