

# MS-100

---



Pipe-to-Pipe Adapter, adapts 1-1/2 in to 3-1/2 in OD pipe to 4 in to 9 in OD pipe

## Product Classification

**Product Type** Adapter

## General Specifications

**Mounting** Pipe-to-pipe

**Tower Taper** Non-tapered

## Dimensions

**Height** 50.8 mm | 2 in

**Width** 304.8 mm | 12 in

**Length** 406.4 mm | 16 in

**Mounting Diameter 2, maximum** 228.6 mm | 9 in

**Mounting Diameter 2, minimum** 101.6 mm | 4 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 38.1 mm | 1.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamp halves | Threaded rod

**Packaging quantity** 2

**Weight, net** 11.3 kg | 24.912 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system