


# MT-198

---



Double Pipe Support Arm with U-bolts, 63 in

## Product Classification

**Product Type** Pipe mount

## General Specifications

**Mounting** Ring mount

## Dimensions

**Height** 406.4 mm | 16 in

**Width** 254 mm | 10 in

**Length** 1,600.2 mm | 63 in

**Pipe Outer Diameter** 114.3 mm | 4.5 in

**Stand-off Distance** 1,600.2 mm | 63 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

**Wind Rating Criteria** Four 72 in x 8 in panel antennas per sector

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Hardware | Stand-off arms

**Packaging quantity** 1

**Weight, net** 46.7 kg | 102.956 lb

# MT-198

---

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--