


# RM-A800

---



Round Member Adapter, 2 in to 10 in

## Product Classification

**Product Type** Clamp set

## Dimensions

**Height** 25.4 mm | 1 in  
**Width** 25.4 mm | 1 in  
**Length** 330.2 mm | 13 in  
**Mounting Diameter, maximum** 254 mm | 10 in  
**Mounting Diameter, minimum** 50.8 mm | 2 in

## Material Specifications

**Material Type** Stainless steel

## Packaging and Weights

**Included** Hose clamp  
**Packaging quantity** 10  
**Weight, net** 0.5 kg | 1.102 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant