


FPCA

Base Product



Fiber Optic Patch Cord, Simplex, Singlemode, 1.2 mm OFNP and LSZH jacket

- SC/UPC, SC/APC, LC/UPC and LC/APC connector versions
- Reduced Bend Radius fiber allows routing in electronic equipment cabinets or bays that commonly provide minimal cable management features
- Compatible with industry standard fiber cable and SC and LC connectors
- G.657.A2 rated glass
- High quality connectors
- OFNP cable
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

1.2 mm fiber optic patch cord assemblies, designed and tested to Telcordia GR409 requirements for small form factor cables, and GR-326 CORE mechanical and performance requirements. Also, designed and tested to the intermateability requirements of IEC 61754-4 and TIA-604-3-B.


Product Classification

Regional Availability	Europe Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber patch cord, simplex
Product Series	FPCA
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Jacket Color	Yellow
Total Fibers, quantity	1
Dimensions	
Cable Assembly Length Range (m)	1 – 99
Cable Assembly Length Range (ft)	1 – 325
Diameter Over Jacket	1.2 mm 0.047 in

Ordering Tree



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2/B2

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

