

16-port multibeam antenna, 8x 698–896 MHz, 2x 2-beam 33° HPBW and 8x 1695–2400 MHz, 2x 2-beam 33° HPBW, 4x RET

- Provides 4T4R capability in low and mid bands
- Full spectrum operation for Band 14, AWS, PCS and WCS bands
- Twin beam patterns are optimized for minimum beam crossover providing for improved LTE data throughput
- Excellent Front-to-Back and SPR performance

General Specifications

Antenna Type	Multibeam
Band	Multiband
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, low band	8
RF Connector Quantity, total	16

Remote Electrical Tilt (RET) Information

CommRET v2
AISG1 8-pin DIN Female AISG1 8-pin DIN Male
1 female 1 male
10-30 Vdc
High band (2) Low band (2)
10 W
2 W
3GPP/AISG 2.0 (Multi-RET)

Page 1 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024



Dimensions

Width	640 mm 25.197 in
Depth	235 mm 9.252 in
Length	1828 mm 71.969 in
Net Weight, without mounting kit	57 kg 125.663 lb

Array Layout

R3	/R4
V1.M2	
Y1/Y2 R1,	<mark> Y3/Y4 </mark> /R2
Left	Right

Array	Freq (MHz)	Conns	RET (MRET)	AISG RET UID
R1	698-896	1-2	1	
R3	698-896	5-6	1	CPxxxxxxxxxxxxXMM1
R2	698-896	3-4	2	CPxxxxxxxxxxxxXMM2
R4	698-896	7-8	2	CPXXXXXXXXXXXXXXXXXXXXXXIVIIVI2
Y1	1695-2400	9-10	3	CPxxxxxxxxxxxxxXMM3
Y3	1695-2400	13-14	5	CPXXXXXXXXXXXXXXXXXXXXXXIVIIVI5
Y2	1695-2400	11-12	4	CPxxxxxxxxxxxxXMM4
Y4	1695-2400	15-16	4	

(Sizes of colored boxes are not true depictions of array sizes)

Bottom

Port Configuration

Page 2 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024





Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2400 MHz 698 – 896 MHz
Polarization	±45°
Total Input Power, maximum	1,500 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	698-806	824-896	1695-1880	1850-1990	1920-2200	2300-2400
Gain, dBi	13.7	14.8	17.7	18.3	19.1	19.1
Beam Centers, Horizontal, degrees	±27	±27	±27	±27	±27	±27
Beamwidth, Horizontal, degrees	42	35	35	33	32	28
Beamwidth, Vertical, degrees	23.7	21.5	7.7	7.3	6.9	6.3
Beam Tilt, degrees	2-20	2-20	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	15	17	16	17	18	22
Front-to-Back Ratio at 180°, dB	26	29	36	37	36	34
Isolation, Cross Polarization, dB	25	25	25	25	25	25

Page 3 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

COMMSCOPE°

Isolation, Inter-band, dB	25	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	200	200	200	200	200	150

Electrical Specifications, BASTA

Frequency Band, MHz	698-806	824-896	1695-1880	1850-1990	1920-2200	2300-2400
Gain by all Beam Tilts, average, dBi	13.1	14.2	17	17.9	18.3	18.5
Gain by all Beam Tilts Tolerance, dB	±0.9	±1	±1	±0.4	±0.8	±1
Beamwidth, Horizontal Tolerance, degrees	±2.7	±3	±2.1	±1.2	±1.9	±1.2
Beamwidth, Vertical Tolerance, degrees	±1.5	±1.1	±0.3	±0.2	±0.4	±0.2
USLS, beampeak to 20° above beampeak, dB			14	16	17	16
Front-to-Back Total Power at 180° ± 30°, dB	21	21	27	29	29	27
CPR at Boresight, dB	17	17	17	19	21	21
CPR at 10 dB Horizontal Beamwidth, dB	6	5	9	13	14	13

Mechanical Specifications

Wind Loading @ Velocity, frontal	764.0 N @ 150 km/h (171.8 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	251.0 N @ 150 km/h (56.4 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	1,039.0 N @ 150 km/h (233.6 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	787.0 N @ 150 km/h (176.9 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	752 mm 29.606 in
Depth, packed	387 mm 15.236 in
Length, packed	1982 mm 78.032 in
Weight, gross	74 kg 163.142 lb

Regulatory Compliance/Certifications

Page 4 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

COMMSCOPE°

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

Included Products

BSAMNT-4

Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

