



## OCAB Outdoor fiber distribution cabinet

- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Serves as a cross-connect or interconnect cabinet with any combination of spliced and connectorized splitters
- A swing handle with half cylinder lock and 3 point latch system prevents unauthorized access
- The standard included base allows easy entry, fixation, identification and sealing of the cables
- Usable 19-inch panel-height is 18 RU + 18 RU with 6 RU + 6 RU for the cable termination plate
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber cross-connect hub
<b>Product Series</b>	OCAB

## General Specifications

<b>Access</b>	Double door   Front
<b>Color</b>	Light Gray (RAL 7035)
<b>Lock Type</b>	Swivel with half cylinder lock (EURO DIN)
<b>Mounting</b>	In-ground root   Pre-fabricated base

## Dimensions

<b>Height</b>	1368 mm   53.858 in
<b>Width</b>	1697 mm   66.811 in
<b>Depth</b>	395 mm   15.551 in
<b>Enclosure Size</b>	Large

## Material Specifications

<b>Finish</b>	Powder coated polyester
<b>Material Type</b>	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

## Environmental Specifications

<b>Environmental Space</b>	Above ground
<b>Qualification Standards</b>	IEC 60529, IP55   IK10

## Packaging and Weights

<b>Included</b>	Base with covers   Blank cable inlet plate   Mounting profiles for shelves
<b>Packaging quantity</b>	2
<b>Packaging Type</b>	Pallet
<b>Note</b>	Two cabinets supplied per Euro pallet, bolted and shrink wrapped in polythene with cardboard hosing protection strapped together for secure shipping