


# 57893-1 | CS54Z3 WHT C7 4/23 S/FTP RL 1000M



Copper Cable, category 7, 4 pair simplex, S/FTP, LSFRZH, XG, 23 AWG solid, 1000 m, white

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable

## General Specifications

<b>ANSI/TIA Category</b>	7
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	S/FTP (shielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	CENELEC EN 50288-4-1   IEC 61156-5 Cat 7   ISO/IEC 11801 Class F

## Dimensions

<b>Cable Length</b>	1,000 m   3,280.84 ft
<b>Diameter Over Insulated Conductor</b>	1.501 mm   0.059 in
<b>Diameter Over Jacket, nominal</b>	7.29 mm   0.287 in
<b>Conductor Gauge, singles</b>	23 AWG

## Electrical Specifications

<b>Characteristic Impedance</b>	100 ohm
<b>Characteristic Impedance Tolerance</b>	±15 ohm
<b>Coupling Attenuation</b>	Type I
<b>dc Resistance, maximum</b>	7.61 ohms/100 m   2.32 ohms/100 ft
<b>Delay Skew, maximum</b>	7 ns
<b>Nominal Velocity of Propagation (NVP)</b>	80 %

# 57893-1 | CS54Z3 WHT C7 4/23 S/FTP RL 1000M

<b>Operating Frequency, maximum</b>	600 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Segregation Class</b>	d
<b>Transfer Impedance</b>	Grade 1

## Electrical Cable Performance

<b>CS</b>	CommScope	<b>NEXT</b>	Near End Crosstalk (dB/100m)
<b>STD</b>	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	<b>PSNEXT</b>	Power Sum Near End Crosstalk (db/100m)
<b>TYP</b>	Typical Electrical Performance	<b>ACRF</b>	Attenuation to Crosstalk Ratio - Far End (dB/100m)
<b>IL</b>	Insertion Loss (dB/100m)	<b>RL</b>	Return Loss (dB)
<b>ACR</b>	Attenuation to Crosstalk Ratio (dB/100m)	<b>ELTCTL</b>	Equal Level Transverse Conversion Transfer Loss (dB/100m)
<b>PSACR</b>	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
<b>PSACRF</b>	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
<b>TCL</b>	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL	ACR	PSNEXT		PSACRF	RL	
	TYP	TYP	STD	TYP	STD	STD	TYP
1	2	94	75	93	75	20	26
4	3.6	92	75	93	75	23	30
10	5.9	90	75	93	75	25	33
16	7.4	88	75	93	73	25	33
20	8.3	87	75	93	71	25	33
31.25	10	86	75	93	67	25	33
62.5	14	82	72.5	93	61	25	33
100	18	78	69.4	93	57	23	33
200	26	67	64.9	90	51	21	29
250	28	64	63.4	89	49	20	28
300	33	57	62.2	87	47	20	27
450	39	39	59.6	85	44	19	26
600	46	34	57.7	77	36	18	25
750	52	28		75	34		24
900	55	17		72	32		23
1,000	57	15		70	30		20

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	Low Smoke Fire Retardant Zero Halogen (LSFRZH)
<b>Shield (Tape) Material</b>	Aluminum/Polyester

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
---------------------------------	------------------------------------

# 57893-1 | CS54Z3 WHT C7 4/23 S/FTP RL 1000M

---

<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Acid Gas Test Method</b>	IEC 60754-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Dca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s2
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d2
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Flame Test Method</b>	IEC 60332-3-22
<b>Smoke Test Method</b>	IEC 61034-2

## Packaging and Weights

<b>Packaging Type</b>	Reel
-----------------------	------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

