

PWRT-210-S

HELIAX® Remote Radio Head Power Cable, 2 conductor with shield, 10 AWG (5.26 mm²), one Red Conductor and one Black Conductor



Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Power cable
Product Brand	HELIAX®
Product Series	PWRT
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Power
Conductor Type, singles	Stranded
Conductors, quantity	2
Construction Type	Discrete power cable Non-armored
Ground Wire Type	Stranded
Jacket Color	Black
Jacket Color, singles	Black Red
Supported Application	Industrial


Dimensions

Diameter Over Conductor, singles, specific	0.1260 in per 105 strands
Diameter Over Dielectric	4.724 mm 0.186 in
Diameter Over Drain Wire, specific	1.8800 in per 7 strands
Diameter Over Ground Wire	3.2 mm 0.126 in
Diameter Over Jacket, nominal	12.395 mm 0.488 in
Diameter Over Jacket, maximum	12.954 mm 0.51 in

PWRT-210-S

Diameter Over Shield (Braid)	10.109 mm 0.398 in
Jacket Thickness	1.143 mm 0.045 in
Conductor Gauge, singles	10 AWG
Drain Wire Gauge	14 AWG
Ground Wire Gauge	10 AWG
Outer Shield (Braid) Gauge	36 AWG

Cross Section Drawing



Electrical Specifications

Conductor dc Resistance	3.478 ohms/km 1.06 ohms/kft
Conductor dc Resistance Note	Maximum value based on a standard condition of 20 °C (68 °F)
Safety Voltage Rating	600 V

Material Specifications

Conductor Material	Tinned copper
Dielectric Material	PVC
Drain Wire Material	Tinned copper
Filler Material	Polypropylene
Ground Wire Material	Tinned copper
Insulation Material, singles	PVC
Jacket Material	PVC
Outer Shield (Braid) Coverage	65 %

PWRT-210-S

Outer Shield (Braid) Material	Tinned copper
Outer Shield (Tape) Material	Aluminum/Poly, non-bonded

Environmental Specifications

Operating Temperature	-40 °C to +90 °C (-40 °F to +194 °F)
Environmental Space	UV resistant for outdoor and/or direct burial installations
Safety Standard	NEC Article 336 (Type TC)

Packaging and Weights

Cable weight	297.633 kg/km 200 lb/kft
---------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Temperature	Specification applicable to non-terminated bulk fiber cable
------------------------------	---