



MJC Copper Closure, unpressurized, gel sealed, cap-ended, for up to 10 /20 pair splices

- Watertight splice closure for aerial, underground and direct buried splices in the unpressurized copper telecommunication network
- Flexible branching plug system allowing installation of cables from 5-pair to 100pair
- Reduced inventory as fewer size closures needed to cover a wide range of applications up to 100 pairs

Product Classification

Regional Availability	EMEA
Product Type	Gel sealed closure
Product Series	MJC

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	2
Cable Sealing Type	Gel filled
Closure Style	Single-ended
Color	Black
Splicing Capacity, maximum	10

Dimensions

Length	185 mm 7.283 in
Single Cable Diameter, maximum	28 mm 1.102 in
Single Cable Diameter, minimum	7 mm 0.276 in
Splice Bundle Diameter, maximum	50 mm 1.969 in

Environmental Specifications

Environmental Space	Aerial Buried
----------------------------	-----------------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

